



EQC632C1W

by Burndy
Catalog ID: EQC632C1W

Prop 65 Notice

Tin Plated Transformer Grounding Connector, RANGES: 8SOL-2STR.

Product Details

General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Hexagonal Bolt
Plating Type	Tin - Hot Dipped
UPC	781810488874
UPC 12 Digit	7818104888744

Dimensions

Dimension - Height inch	1.44 in
Dimension - L Length Overall mm	37 mm
Dimension - Length Overall inch	1.44 in
Dimension - Stud Size inch	25/64
Dimension - Width inch	0.90 in
Dimension - Width mm	23 mm

Conductor Related

Conductor - Copper Solid Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Size Range	8 AWG-2 AWG
Conductor - Copper Str Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size Range	8 AWG-2 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)