



ES25A2W

by Burndy
Catalog ID: ES25A2W

Prop 65 Notice

SIDE A: 1/0STR ALUM COLOR: YELLOW SIDE B: 4 ACSR, 3,4STR AL-CU,
2SOL AL-CU COLOR: ORANGE

Product Details

General

Color Code - Side A	Yellow
Color Code - Side B	Orange
Die Index	BG or 5/8
Insulation	Y
Insulation Type	Nylon
Material	Aluminum
Plated	Y
Plating Type	Tin - Hot Dipped
Prefilled Oxide Inhibitor	Y
Trade Name	INSULINK™
Type	Insulated Service Entrance Connectors
UPC	781810000373
UPC 12 Digit	7818100003733

Dimensions

Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.75 in
Dimension - Outside Diameter inch	.75 in

Conductor Related

Conductor - ACSR Str Size B	4 (6/1) Swan AWG;4 (7/1) Swanate AWG
Conductor - ACSR Str Size B Range	4 (6/1) Swan AWG-4 (7/1) Swanate AWG
Conductor - AL Str Size A	1/0 AWG
Conductor - AL Str Size A Range	1/0 AWG
Conductor - AL Str Size B	4 AWG;3 AWG
Conductor - AL Str Size B Range	4 AWG-3 AWG
Conductor - Copper Solid Size B	2 AWG
Conductor - Copper Str Size A	1/0
Conductor - Copper Str Size A Range	1/0
Conductor - Copper Str Size B	4 AWG;3 AWG
Conductor - Copper Str Size B Range	4 AWG-3 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	5000
-----------------------	------

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)