



## ES25A4W

by Burndy  
Catalog ID: ES25A4W

Prop 65 Notice

SIDE A: 1/0STR AL-CU COLOR: YELLOW SIDE B: 6 ACSR, 5,6STR AL-CU,  
4SOL AL-CU COLOR: BLUE

## Product Details

### General

Color Code - Side A	Yellow
Color Code - Side B	Blue
Die Index	BG or 5/8
Insulation	Y
Insulation Type	Nylon
Material	Aluminum
Plated	Y
Plating Type	Tin - Hot Dipped
Prefilled Oxide Inhibitor	Y
Trade Name	INSULINK™
Type	Insulated Service Entrance Connectors
UPC	781810097977
UPC 12 Digit	7818100979777

### Dimensions

Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.75 in
Dimension - Outside Diameter inch	.75 in

### Conductor Related

Conductor - ACSR Str Size B	6 (6/1) Turkey AWG
Conductor - ACSR Str Size B Range	6 (6/1) Turkey AWG
Conductor - AL Str Size A	1/0 AWG
Conductor - AL Str Size A Range	1/0 AWG
Conductor - AL Str Size B	6 AWG;5 AWG
Conductor - AL Str Size B Range	6 AWG-5 AWG
Conductor - Copper Solid Size B	4 AWG
Conductor - Copper Str Size A	1/0
Conductor - Copper Str Size A Range	1/0
Conductor - Copper Str Size B	6 AWG;5 AWG
Conductor - Copper Str Size B Range	6 AWG-5 AWG

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	100 EA
Minimum Pack Quantity	1

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)