



ES25R2WG1

by Burndy
Catalog ID: ES25R2WG1

Prop 65 Notice

KIT CONTAINS: (2) ES25R2W & (1) YSU25R2W YELLOW:1/0 & 1 ACSR,1/0
& 1-19 STR CU/AL ORANGE:4 ACSR, 3 & 4 STR & 2 SOL CU/AL

Product Details

General

Die Index	BG
Insulation	Y
Insulation Type	Nylon
Material	Aluminum
Plated	Y
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Type	Insulated Service Entrance Connectors
UPC	781810103722
UPC 12 Digit	7818101037222

Dimensions

Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.75 in
Dimension - Outside Diameter inch	.75 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)