



ES2R2RBOX

by Burndy
Catalog ID: ES2R2RBOX

Prop 65 Notice

ACSR: #2, AL/CU: #2 STR - #1 STR AL/CU: #2 STR - #1 STR INDEX: BG OR
5/8" TOOLS: OH25, MD6-RED-RED

Product Details

General

Die Index	BG
Insulation	Y
Insulation Type	Nylon
Material	Aluminum
Plated	Y
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	INSULINK™
Type	Insulated Service Entrance Connectors
UPC	781810191750
UPC 12 Digit	7818101917500

Dimensions

Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.75 in
Dimension - Outside Diameter inch	.75 in

Conductor Related

Conductor - ACSR Str Size A	2 AWG
Conductor - ACSR Str Size B	2 AWG
Conductor - AL Str Size A	1 STR, 2 STR
Conductor - AL Str Size B	1 STR, 2 STR
Conductor - Copper Str Size A	1 STR, 2 STR
Conductor - Copper Str Size B	1 STR, 2 STR

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)