



ES2R4R

by Burndy
Catalog ID: ES2R4R

Prop 65 Notice

RUN/COURSE TAP/DERIVATION ACSR:4 S.B. 200%|6 S.B. 200% AL & CU:2 STR.-2 STR|4 STR.-4 STR. COLOR/COULEUR: A-RED, B-ORANGE

Product Details

General

Die Index	BG
Insulation	Y
Insulation Type	Nylon
Material	Aluminum
Plated	Y
Plating Type	Tin - Hot Dipped
Prefilled Oxide Inhibitor	Y
Trade Name	INSULINK™
Type	Insulated Service Entrance Connectors
UPC	781810420430
UPC 12 Digit	7818104204300

Dimensions

Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.75 in
Dimension - Outside Diameter inch	.75 in

Conductor Related

Conductor - ACSR Str Size A	2 AWG
Conductor - ACSR Str Size B	4 AWG
Conductor - AL Str Size A	2 AWG
Conductor - AL Str Size B	4 AWG
Conductor - Copper Str Size A	2 AWG
Conductor - Copper Str Size B	4 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)