



## FCB634N

by Burndy  
Catalog ID: FCB634N

Prop 65 Notice

Transformer tap adapter, Tin plated.

Transformer tap adapters, designed to accommodate from 1 to 6 nema drilled copper or aluminum terminal taps from a single secondary transformer outlet

## Product Details

### General

Application	Substation
Connector Type	T-Connector
Material	Copper
Physical Attribute - Number of Holes	4
Plated	Y
Plating Type	Tin
Sub Brand	XFMR CONN
Type	T-Connector
UPC	781810002094
UPC 12 Digit	7818100020944

### Dimensions

Dimension - Height fraction	5-1/4 in
Dimension - Height inch	5.25 in
Dimension - L Length Overall mm	95 mm
Dimension - Length Overall inch	3.75 in
Dimension - P inch	2.25 in
Dimension - Pin Diameter fraction	1/2 in
Dimension - Pin Diameter inch	.50 in

### Electrical Ratings

Rating - KVA	230 kV
--------------	--------

### Conductor Related

Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Size</li> <li>• CU C Solid-Size</li> </ul>
----------------	----------------------------------------------------------------------------------------------

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)