

# FL1825X03B

by Burndy  
Catalog ID: FL1825X03B

Prop 65 Notice

Brass Flag Style Female Quick Disconnect, 22-18 AWG, Tin Plated, Bulk Packaging



## Product Details

### General

Connector Type	Female Disconnect
Material	Brass
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810327845
UPC 12 Digit	7818103278455

### Dimensions

Dimension - B Length fraction	1/4 in
Dimension - B Length inch	0.25 in
Dimension - Length Overall inch	0.50 in
Dimension - Outside Diameter inch	0.13 in
Dimension - Width inch	0.25 in
Dimension - Width mm	6 mm

### Conductor Related

Conductor - Copper Str Size	20 AWG;18 AWG
Conductor - Copper Str Size Range	20 AWG-18 AWG
Conductor Type	CU C Str-Size

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1000
-----------------------	------

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)