



FLN1425X03D

by Burndy
Catalog ID: FLN1425X03D

Prop 65 Notice

Brass Female Quick Disconnect, Snap Together, Side Entrance Chamfer, 16-14 AWG.

Nylon flag-style female quick disconnect, provide quick, reliable snap-together interconnections without the use of tools

Product Details

General

Application	Female Disconnect
Connector Type	Female Disconnect
Insulation	Y
Insulation Type	Nylon
Material	Brass
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810525623
UPC 12 Digit	7818105256233

Dimensions

Dimension - B Length inch	0.40 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.25 in
Dimension - Width mm	6 mm

Conductor Related

Conductor Range	#16 AWG to #14 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	600 EA
Minimum Pack Quantity	50

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)