


FQN10F25X03D

by Burndy
Catalog ID: FQN10F25X03D

Prop 65 Notice

Brass Fully Insul Female Quick Disconnects, Funnel Entry, 10-12 AWG, 300 V, 0.98" L, 0.25" W, Nylon Insul, Tin Plated, Yellow(Insul Color).

Features: Fully Insulated Connectors: Eliminate The Need For Post Installation Insulation, Funnel Entry Barrel Opening: Assures Quick And Easy Wire Insertion, Dimpled Female Socket Detent: Ensures Firm Grip, 300 V Maximum, 105 DEG C Maximum, Installation Tool: Y10D Tool, Size: 0.41 IN Width X 0.99 IN Overall Length, Temperature: 105 DEG C Maximum, Nema Tab Size: 0.25 X 032 IN



Product Details

General

Application	For quickly connecting or disconnecting a terminal
Connector Type	Female Disconnect
Insulation	Y
Insulation Type	Nylon
Material	Brass
Plated	Y
Plating Type	Tin
Sub Brand	FINGRIP
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810293058
UPC 12 Digit	7818102930588

Dimensions

Dimension - Length Overall inch	0.98 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.25 in
Dimension - Width mm	6 mm

Electrical Ratings

Voltage - Maximum	300 V
-------------------	-------

Conductor Related

Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	300 EA
Minimum Pack Quantity	25

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)