

FQP18F25X03D

by Burndy
Catalog ID: FQP18F25X03D

Prop 65 Notice

Vinyl Fully Insulated Brass Female Quick Disconnects, 22 - 18 AWG



Product Details

General

Connector Type	Female Disconnect
Insulation	Y
Insulation Type	Vinyl
Material	Brass
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810292952
UPC 12 Digit	7818102929522

Dimensions

Dimension - Length Overall inch	0.90 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.25 in
Dimension - Width mm	6 mm

Conductor Related

Conductor - Copper Str Size	20 AWG;18 AWG
Conductor - Copper Str Size Range	20 AWG-18 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Carton Quantity	600 EA
-----------------	--------

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)