

FT3B4/0

by Burndy
Catalog ID: FT3B4/0

Prop 65 Notice

Power Distribution Block, Max. 2 Wires per Phase, 3/0-4/0 AWG (Run), 6-4/0 AWG (Tap)



Product Details

General

Hex Size	1/4
Installation Torque Recommended in-lb	200 LBS/in
Number Of Poles	3
Temperature Rating	194
Trade Name	U-BLOK™
UPC	781810113721
UPC 12 Digit	7818101137211

Dimensions

Dimension - Height fraction	4-1/8
Dimension - Height inch	4.13 in
Dimension - L Length Overall mm	149 mm
Dimension - Length Overall inch	5.88 in
Dimension - Width fraction	3-7/8 in
Dimension - Width inch	3.88 in
Dimension - Width mm	99 mm
Weight	1.25 lb

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Run	3/0 AWG;4/0 AWG
Conductor - AL Str Run Range	3/0-4/0 AWG
Conductor - AL Str Tap	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - AL Str Tap Range	6-4/0 AWG
Conductor - Copper Str Run	3/0 AWG;4/0 AWG
Conductor - Copper Str Run Range	3/0-4/0 AWG
Conductor - Copper Str Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Tap Range	6-4/0 AWG
Number Of Conductors	2

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)