

FT4B500

by Burndy
Catalog ID: FT4B500

Prop 65 Notice

Power Distribution Block, 4 Poles, 2 Wires/Phase, 7.88" L, 400-500 kcmil(Run), #6-500 kcmil(Tap)



Product Details

General

Hex Size	3/8
Installation Torque Recommended in-lb	375 LBS/in
Temperature Rating	194
Trade Name	U-BLOK™
UPC	781810113585
UPC 12 Digit	7818101135855

Dimensions

Dimension - Height fraction	4-1/8
Dimension - Height inch	4.13 in
Dimension - L Length Overall mm	200 mm
Dimension - Length Overall inch	7.88 in
Dimension - Width fraction	3-7/8 in
Dimension - Width inch	3.88 in
Dimension - Width mm	200 mm
Weight	2.75 lb

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Run Range	400-500 Kcmil
Conductor - AL Str Tap Range	6-500 kcmil
Conductor - Copper Str Run Range	400-500 Kcmil
Conductor - Copper Str Tap Range	6-500 kcmil
Number Of Conductors	2

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)