

# FTU1

by Burndy  
Catalog ID: FTU1

Flexi U-Tap Assy, #2 - #1 AWG Cu/Al (Run), #12-#1 AWG Cu/Al (Tap)



## Product Details

### General

Installation Torque Recommended in-lb	100 in-lb
Temperature Rating	194° F
Trade Name	FLEXITAP™
UPC	781810112588
UPC 12 Digit	7818101125888

### Dimensions

Dimension - Height inch	1.44
Dimension - L Length Overall mm	19
Dimension - Length Overall inch	0.75
Dimension - Width mm	25 mm

### Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

### Conductor Related

Conductor - AL Str Run Range	1 AWG -2 AWG
Conductor - AL Str Tap Range	1 AWG - 12 AWG
Conductor - Copper Str Run Range	1 AWG -2 AWG
Conductor - Copper Str Tap Range	1 AWG - 12 AWG

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

### Logistics

Minimum Pack Quantity	7500
-----------------------	------

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)