

FTU2/0

by Burndy
Catalog ID: FTU2/0

BURNDY; Distribution Block; U-TAP; Flexitap; Tap Size: 12 - 2/0 AWG;
Conductor Size: 2/0 - 1/0 AWG Run; Conductor Type: Aluminum/Copper



Product Details

General

Installation Torque Recommended in-lb	100 in-lb
Temperature Rating	194° F
Trade Name	FLEXITAP™
UPC	781810112656
UPC 12 Digit	7818101126566

Dimensions

Dimension - Height inch	1.63
Dimension - L Length Overall mm	25
Dimension - Length Overall inch	1
Dimension - Width mm	28 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Run Range	1/0 AWG - 2/0 AWG
Conductor - AL Str Tap Range	12 AWG - 2/0 AWG
Conductor - Copper Str Run Range	1/0 AWG - 2/0 AWG
Conductor - Copper Str Tap Range	12 AWG - 2/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	2520
-----------------------	------

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)