

FTU350

by Burndy
Catalog ID: FTU350

Flexi U-Tap Assy, 250 - 350 Kcmil Cu/Al (Run), #6 AWG- 350 Kcmil Cu/Al (Tap)



Product Details

General

Installation Torque Recommended in-lb	200 in-lb
Temperature Rating	194° F
Trade Name	FLEXITAP™
UPC	781810113714
UPC 12 Digit	7818101137144

Dimensions

Dimension - Height inch	2.31
Dimension - L Length Overall mm	44
Dimension - Length Overall inch	1.74
Dimension - Width mm	40 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Run Range	250 kcmil -350 kcmil
Conductor - AL Str Tap Range	6 AWG - 350 kcmil
Conductor - Copper Str Run Range	250 kcmil -350 kcmil
Conductor - Copper Str Tap Range	6 AWG - 350 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)