

FTU4/0

by Burndy
Catalog ID: FTU4/0

Prop 65 Notice

BURNDY; Distribution Block; U-TAP; Flexitap; Conductor Size: 4/0 - 3/0 AWG Run; Tap Size: 6 - 4/0 AWG; Conductor Type: Aluminum/Copper



Product Details

General

Installation Torque Recommended in-lb	200 in-lb
Temperature Rating	194° F
Trade Name	FLEXITAP™
UPC	781810113653
UPC 12 Digit	7818101136533

Dimensions

Dimension - Height inch	2
Dimension - L Length Overall mm	38
Dimension - Length Overall inch	1.5
Dimension - Width mm	32 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Run Range	3/0 AWG - 4/0 AWG
Conductor - AL Str Tap Range	6 AWG -4/0 AWG
Conductor - Copper Str Run Range	3/0 AWG - 4/0 AWG
Conductor - Copper Str Tap Range	6 AWG -4/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)