

FTU500MT

by Burndy
Catalog ID: FTU500MT

Flexi U-Tap Assy, Mountable, 3/0 AWG - 500 Kcmil Cu/Al (Run), #6 - 1/0 AWG Cu/Al (Tap)



Product Details

General

Installation Torque Recommended in-lb	110 in-lb
Temperature Rating	194° F
UPC	781810112793
UPC 12 Digit	7818101127933

Dimensions

Dimension - L Length Overall mm	59
Dimension - Length Overall inch	2.31
Dimension - Width mm	40.39

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Run Range	3/0 AWG- 500 kcmil
Conductor - AL Str Tap Range	6 AWG - 1/0 AWG
Conductor - Copper Str Run Range	3/0 AWG- 500 kcmil
Conductor - Copper Str Tap Range	6 AWG - 1/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)