



GA25H26TN

by Burndy
Catalog ID: GA25H26TN

Prop 65 Notice

FOR CABLE TO H BEAM TIN PLATED CABLE: 4SOL - 2/0STR H BEAM: (1-7/8 x 1-7/8) TO (2-1/2 x 2-1/2)

Product Details

General

Installation Torque Recommended Run in-lb	240 Lb in
Material	Copper
Plated	Y
Plating Type	Tin Plated
UPC	781810562185
UPC 12 Digit	7818105621855

Dimensions

Dimension - Height fraction	4-3/4 in
Dimension - Height inch	4.75 in
Dimension - Width inch	4 in
Dimension - Width mm	102 mm

Conductor Related

Conductor - Copper Solid Size	4 AWG
Conductor - Copper Str Size	2/0 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)