



## GA25H29TN

by Burndy  
Catalog ID: GA25H29TN

Prop 65 Notice

Tin plated

### Product Details

#### General

Installation Torque Recommended Run in-lb	240 Lb in
Material	Copper
Plated	Y
Plating Type	Tin Plated
UPC	621945462724
UPC 12 Digit	781810415146

#### Dimensions

Dimension - Height fraction	4-3/4 in
Dimension - Height inch	4.75 in
Dimension - Width inch	4 in
Dimension - Width mm	102 mm

#### Conductor Related

Conductor - Copper Solid Size	2/0 AWG
Conductor - Copper Str Size	250 kcmil
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

#### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	EX

#### Logistics

Carton Quantity	20 EA
Minimum Pack Quantity	1

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)