



GAR1729TN

by Burndy
Catalog ID: GAR1729TN

Prop 65 Notice

To Rod or Pipe with the Same Connector.

Product Details

General

Installation Torque Recommended Run in-lb	240 Lb in
Installation Torque Recommended in-lb	240 LBS/in
Material	Copper
Material - Hardware	DURIUM™ Silicon Bronze
Plated	Y
Plating Type	Tin plated
U Bolt Type	268
UPC	781810246887
UPC 12 Digit	7818102468877

Dimensions

Dimension - B Length inch	2.31 in
Dimension - Height inch	4.00 in
Dimension - L Length Overall mm	46 mm
Dimension - Length Overall inch	1.81 in
Dimension - Outside Diameter inch	1.90 in
Dimension - Width inch	3.25 in
Dimension - Width mm	83 mm

Conductor Related

Conductor - Copper Solid Size	2/0 AWG
Conductor - Copper Solid Size Range	2/0-4/0
Conductor - Copper Str Size	250 Kcmil
Conductor - Copper Str Size Range	1/0-250
Conductor - Copper Tube Std Size	1 1/2
Conductor - Copper Tube Std Size Range	1 1/2
Conductor - Pipe or Round Tube Size Range	1-1/2 in
Conductor - Rod Size	1.620-1.90 in
Conductor - Rod Size Range	1 5/8-1 7/8

Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size
----------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	14
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)