



GAR1829G1TN

by Burndy
Catalog ID: GAR1829G1TN

Prop 65 Notice

Ground Clamp Copper Tin plated 2/0 AWG-250 Kcmil Installation Torque
Recommended Run in-lb240 LB in

Product Details

General

Installation Torque Recommended Run in-lb	240 Lb-in
Material	Copper
Plated	Y
Plating Type	Tin plated
UPC	781810541210
UPC 12 Digit	7818105412100

Conductor Related

Conductor - Copper Solid Size	2/0 AWG
Conductor - Copper Str Size	250 Kcmil
Conductor - Pipe or Round Tube Size Range	2 in
Conductor - Rod Size	2 in-2.38 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)