



GAR2026TN

by Burndy
Catalog ID: GAR2026TN

Prop 65 Notice

Mechanical Grounding Connector, Cable to Rod or Pipe, 4 AWG (Sol)-2/0 AWG (Str), 3" Pipe, 3"-3-1/2" Rod, Tin Plated.

Product Details

General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Plated	Y
Plating Type	Tin - Electro Plated
U Bolt Type	267
UPC	621945133846
UPC 12 Digit	6219451338466

Dimensions

Dimension - B Length inch	3.50 in
Dimension - Height inch	5.62 in
Dimension - L Length Overall mm	40 mm
Dimension - Length Overall inch	1.56 in
Dimension - Outside Diameter inch	3.50 in
Dimension - Width inch	4.81 in
Dimension - Width mm	122 mm

Conductor Related

Conductor - Copper Solid Size	4;3;2;1;1/0;2/0;3/0
Conductor - Copper Solid Size Range	4 AWG-2/0 AWG
Conductor - Copper Str Size	5;4;3;2;1;1/0;2/0
Conductor - Copper Str Size Range	5-2/0
Conductor - Copper Tube Std Size	3;3 1/2
Conductor - Copper Tube Std Size Range	3-3 1/2
Conductor - Pipe or Round Tube Size	3 in
Conductor - Rod Size	3 - 3.5 in
Conductor - Rod Size Range	3
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)