



GAR2434

by Burndy
Catalog ID: GAR2434

Prop 65 Notice

Mechanical Grounding Connector, Cable to Rod or Pipe, 300 - 500 kcmil,
5" Pipe, Bright Dipped.

Product Details

General

| | |
|---------------------------------------|------------------------|
| Installation Torque Recommended in-lb | 480 LBS/in |
| Material | Copper Alloy |
| Material - Hardware | DURIUM™ Silicon Bronze |
| Plated | N |
| Plating Type | Bright Dipped |
| U Bolt Type | 437 |
| UPC | 781810001462 |
| UPC 12 Digit | 7818100014622 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - B Length inch | 5.50 in |
| Dimension - Height fraction | 8-5/8 in |
| Dimension - Height inch | 8.63 in |
| Dimension - L Length Overall mm | 60 mm |
| Dimension - Length Overall inch | 2.38 in |
| Dimension - Outside Diameter inch | 5.56 in |
| Dimension - Width fraction | 7-1/4 in |
| Dimension - Width inch | 7.25 in |
| Dimension - Width mm | 184 mm |

Conductor Related

| | |
|--|--|
| Conductor - Copper Solid Size Range | 300 Kcmil -500 Kcmil |
| Conductor - Copper Str Size | 300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil |
| Conductor - Copper Str Size Range | 300 kcmil-500 kcmil |
| Conductor - Copper Tube Std Size | 5 IPS IPS |
| Conductor - Copper Tube Std Size Range | 5 IPS IPS |
| Conductor - Pipe or Round Tube Size | 5 in |
| Conductor Type | <ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size |

Certifications and Compliance

| | |
|---|-------|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Listed Direct Burial | Yes |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | EX |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)