



GAR3903BUW

by Burndy
Catalog ID: GAR3903BUW

Prop 65 Notice

#4 - 4/0 AWG; 1-1/4" to 2" Pipe; 3/8 " Stud; tin plated; UL/CSA; Rated for Direct Burial

Product Details

General

Installation Torque Recommended in-lb	200 LBS/in
Material	Bronze, Silicon (DURIUM is a trademark)
Material - Hardware	Copper Alloy
Plated	N
Plating Type	Unplated
UPC	781810569894
UPC 12 Digit	7818105698944

Conductor Related

Conductor - Copper Solid Size Range	4 AWG - 4/0 AWG
Conductor - Pipe or Round Tube Size	1.25 - 2 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)