



## GAR3906BUTN

by Burndy  
Catalog ID: GAR3906BUTN

Prop 65 Notice

ACTUAL O.D.: 6.62 in. [168] 4 Str (.232) - 4/0 Str (.528) AWG 25mm<sup>2</sup> Str  
[6.6] - 95mm<sup>2</sup> str [12.0] TQ: 200 lb-in [22.5 Nm] Tin Plated

## Product Details

### General

|                                       |                    |
|---------------------------------------|--------------------|
| Installation Torque Recommended in-lb | 200 lb-in          |
| Material                              | Copper Alloy       |
| Plated                                | N                  |
| Plating Type                          | Tin Electro Plated |
| UPC                                   | 781810501115       |
| UPC 12 Digit                          | 7818105011155      |

### Dimensions

|                                   |         |
|-----------------------------------|---------|
| Dimension - Height inch           | 8.50 in |
| Dimension - Length Overall inch   | 1.75 in |
| Dimension - Outside Diameter inch | 6.62 in |

### Conductor Related

|                                     |                 |
|-------------------------------------|-----------------|
| Conductor - Copper Solid Size Range | 4 AWG - 4/0 AWG |
| Conductor - Pipe or Round Tube Size | 6 in            |

### Certifications and Compliance

|                                    |     |
|------------------------------------|-----|
| Certification - CSA Approved       | No  |
| Certification - ETL                | No  |
| Certification - UL Recognized      | No  |
| Certification - cULus              | No  |
| Standards - RoHS Compliance Status | CM  |
| UL Listed                          | Yes |

### Logistics

|                       |    |
|-----------------------|----|
| Minimum Pack Quantity | 12 |
|-----------------------|----|

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)