



GAR3909TC

by Burndy
Catalog ID: GAR3909TC

Prop 65 Notice

Mechanical Ground Connector, For 2 Hole Lug to Water Pipe or Rod, 12" IPS, 3/8" Bolt

Product Details

General

Installation Torque Recommended in-lb	240 lb-in
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Number of Holes	3
Physical Attribute - Pad Configuration	3.63 x 2.67 - 3 Holes
Plated	N
Plating Type	Unplated
Type	Rod or Tube Clamp with Mounting Pad
U Bolt Type	1030
UPC	781810001622
UPC 12 Digit	7818100016222

Dimensions

Dimension - Bolt Size fraction	3/8
Dimension - Height inch	14.00 in
Dimension - Length Overall inch	3.63 in
Dimension - Outside Diameter inch	12.75 in
Dimension - Thread Size	3/8-16
Dimension - Threads per inch	16
Dimension - Width inch	15.25 in
Dimension - Width mm	387 mm

Conductor Related

Conductor - Copper Tube EH Size	12
Conductor - Pipe or Round Tube Size	12 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No

Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)