



GAR655CG1

by Burndy
Catalog ID: GAR655CG1

Prop 65 Notice

Ground Clamp

Product Details

General

Installation Torque Recommended in-lb	240
Material	Copper Alloy
Plated	N
Plating Type	Unplated
UPC	621945157415
UPC 12 Digit	6219451574155

Conductor Related

Conductor - Copper Str Size	2/0 copper cable
Conductor - Rod Size Range	1" Copper water tube

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)