

GB29CG40

by Burndy
Catalog ID: GB29CG40

Prop 65 Notice

WIRE/CABLE: 2.0 SOL.- 250MCM



Product Details

General

Installation Torque Recommended in-lb	40
Material	Copper Alloy, Cast
Material Type - Screw	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
UPC	781810422014
UPC 12 Digit	7818104220144

Dimensions

Dimension - Height inch	2.32 in
Dimension - L Length Overall mm	32 mm
Dimension - Length Overall inch	1.25 in
Dimension - Width fraction	1-7/8 in
Dimension - Width inch	1.88 in

Conductor Related

Conductor - Copper Solid Size	2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Size Range	2/0 AWG-4/0 AWG
Conductor - Copper Str Size	2/0 Sol to 250MCM
Conductor - Copper Str Size Range	2/0 AWG-250 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	28
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)