



GB29G69

by Burndy
Catalog ID: GB29G69

Prop 65 Notice

Mechanical Ground Connector

Product Details

General

| | |
|---------------------------------------|--------------------|
| Installation Torque Recommended in-lb | 480 |
| Material | Copper Alloy, Cast |
| Plated | N |
| Plating Type | Unplated |
| UPC | 781810001790 |
| UPC 12 Digit | 7818100017900 |

Conductor Related

| | |
|-----------------------------|--------------------|
| Conductor - Copper Str Size | AWG2/0 to 250Kcmil |
|-----------------------------|--------------------|

Certifications and Compliance

| | |
|---|-------|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Listed Direct Burial | Yes |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | EX |
| UL Listed | No |

Logistics

| | |
|-----------------------|----|
| Minimum Pack Quantity | 24 |
|-----------------------|----|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)