

## GB34TN

by Burndy  
Catalog ID: GB34TN

Prop 65 Notice

Mechanical Grounding Connector, Cable to 1/4" Thick Bar, 300 kcmil - 500 kcmil, 1/2" Stud, 2-1/3 IN Width Tin Plated



## Product Details

### General

Installation Torque Recommended in-lb	480 lb-in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	Y
Plating Type	Tin - Electro Plated
UPC	781810100905
UPC 12 Digit	7818101009055

### Dimensions

Dimension - Height inch	2.57 in
Dimension - L Length Overall mm	35 mm
Dimension - Length Overall inch	1.38 in
Dimension - Width fraction	2-1/3 in
Dimension - Width inch	2.31 in

### Conductor Related

Conductor - Copper Solid Size Range	300 KCMIL - 500 KCMIL
Conductor - Copper Str Size	300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	300 kcmil-500 kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Minimum Pack Quantity	24
-----------------------	----

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)