

GB44T10W

by Burndy
Catalog ID: GB44T10W

Prop 65 Notice

Mechanical Grounding Connector, Cable to 1/4" - 1 1/4" Thick Bar, 800 kcmil - 1000 kcmil, 5/8" Stud, 3-1/6 IN Width Tin Hot Dipped



Product Details

General

Installation Torque Recommended in-lb	660 lb-in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Oval Shank Bolt
Plated	Y
Plating Type	Tin - Hot Dipped
UPC	781810116890
UPC 12 Digit	7818101168900

Dimensions

Dimension - B Length inch	1.75 in
Dimension - Height inch	4.28 in
Dimension - L Length Overall mm	45 mm
Dimension - Length Overall inch	1.75 in
Dimension - Width fraction	3-1/6 in
Dimension - Width inch	3.16 in

Conductor Related

Conductor - Copper Solid Size Range	800 KCMIL - 1000 KCMIL
Conductor - Copper Str Size	800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Size Range	800 kcmil-1000 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	2
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)