



## GBG28G1

by Burndy  
Catalog ID: GBG28G1

Prop 65 Notice

Copper Ground Connector CU CABLE: 8 AWG (SOL) - 4 AWG (STR) 5/16"  
Stud

## Product Details

### General

|                                 |                   |
|---------------------------------|-------------------|
| Material Type - Screw           | Steel - Stainless |
| Physical Attribute - Screw Type | Hexagonal Bolt    |
| Plated                          | N                 |
| Plating Type                    | Unplated          |
| UPC                             | 781810096208      |
| UPC 12 Digit                    | 7818100962088     |

### Dimensions

|                            |          |
|----------------------------|----------|
| Dimension - B Length inch  | 1.19 in  |
| Dimension - Width fraction | 7-1/8 in |
| Dimension - Width inch     | 7.12 in  |

### Conductor Related

|                                     |   |
|-------------------------------------|---|
| Conductor - Copper Solid Size       | 4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG |
| Conductor - Copper Solid Size Range | 4 AWG-4/0 AWG   |
| Conductor - Copper Str Size         | 4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG    |
| Conductor - Copper Str Size Range   | 4 AWG-4/0 AWG   |

### Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Certification - cULus              | No |
| Standards - RoHS Compliance Status | EX |
| UL Listed                          | No |

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)