



GBM34T8

by Burndy
Catalog ID: GBM34T8

Prop 65 Notice

Mechanical Grounding Connector, Cable to 1/2" - 1" Thick Bar, 300 kcmil - 500 kcmil, 1/2" Stud.

Product Details

General

Installation Torque Recommended in-lb	480 lb-in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
UPC	781810079379
UPC 12 Digit	7818100793799

Dimensions

Dimension - L Length Overall mm	35 mm
Dimension - Length Overall inch	1.38 in
Dimension - Width fraction	2-2/9 in
Dimension - Width inch	2.22 in
Dimension - Width mm	56 mm

Conductor Related

Conductor - Copper Solid Size Range	300 KCMIL - 500 KCMIL
Conductor - Copper Str Size	300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	300 kcmil-500 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)