



GBM39W

by Burndy
Catalog ID: GBM39W

Prop 65 Notice

Mechanical Grounding Connector, Cable to 1/4" Thick Bar, 550 kcmil - 750 kcmil, 5/8" Stud, Tin Hot Dipped

Product Details

General

Installation Torque Recommended in-lb	660 lb-in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	Y
Plating Type	Tin - Hot Dipped
UPC	781810123614
UPC 12 Digit	7818101236144

Dimensions

Dimension - B Length inch	1.75 in
Dimension - Height inch	3.31 in
Dimension - L Length Overall mm	44 mm
Dimension - Length Overall inch	1.75 in
Dimension - Width fraction	2-2/3 in
Dimension - Width inch	2.69 in
Dimension - Width mm	68 mm

Conductor Related

Conductor - Copper Solid Size Range	550 KCMIL - 750 KCMIL
Conductor - Copper Str Size	550 kcmil;600 kcmil;700 kcmil;750 kcmil
Conductor - Copper Str Size Range	550 kcmil-750 kcmil

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)