



GC18A

by Burndy
Catalog ID: GC18A

Prop 65 Notice

Mechanical Grounding Connector, Cable to Water Pipe, 6 AWG - 250 kcmil, 1-1/4" - 2" Pipe, Al/Cu Rated.

Features: Ground Clamps Are UL Listed For Use With Either Copper Or Aluminum Conductors To Copper Water Pipe, Galvanized Pipe Or Steel Conduit, All Clamps Are Constructed From Tin-Plated High Strength Extruded Aluminum Alloy, PENETROX Oxide Inhibiting Compounds Are Recommended For All Aluminum, Clamps Are Dual Rated For Both Copper And Aluminum Conductors: Maximum Flexibility Of Application, All Connectors Are Tin Plated: Provide Low Contact Resistance And Prevents Galvanic Corrosion, All Clamps Are Range Taking: Only 3 Catalog Numbers Covers Complete Range Of Applications From 1/2 4 IN, Set Screw Type: Hex Socket, Length: 3-3/4 IN, Hex Size: 5/16 IN, Width: 13/16 IN

Product Details

General

Application	For Use With Either Copper Or Aluminum Conductors To Copper Water Pipe, Galvanized Pipe Or Steel Conduit
Hex Size	5/16
Installation Torque Recommended in-lb	180 LBS/in
Material	Aluminum
Material Type - Screw	Steel
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	Y
Plating Type	Tin
Sub Brand	MECHANICAL CONNECTOR
Temperature Rating	194
Type	GC-A, Dual Rated
UPC	781810240014
UPC 12 Digit	7818102400144

Dimensions

Dimension - Hole Size inch	0.62 in
Dimension - Hole Size mm	16 mm
Dimension - L Length Overall mm	95 mm
Dimension - Length Overall inch	3.75 in
Dimension - Pad Width inch	0.81 in
Dimension - Width fraction	13/16 in
Dimension - Width inch	0.81 in
Dimension - Width mm	21 mm

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - AL Str Size	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - AL Str Size Range	6 AWG-250 kcmil
Conductor - Copper Solid Size	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Size Range	6 AWG-4/0 AWG
Conductor - Copper Str Size	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Size Range	6 AWG-250 kcmil
Conductor - Pipe or Round Tube Run	1 1/4 ;1 1/2 ;2
Conductor - Pipe or Round Tube Run Range	1 1/4 -2
Conductor Type	<ul style="list-style-type: none">• AL C Str-Size• CU C Solid-Size• CU C Str-Size• Pipe or Tube Round-Run

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	80 EA
Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)