



GC4444

by Burndy
Catalog ID: GC4444

Prop 65 Notice

Mechanical Grounding Connector, 2 Copper Cables to 1/4" Thick Bar, 800 kcmil - 1000 kcmil, 5/8" Stud

Product Details

General

Installation Torque Recommended in-lb	660 lb-in
Material	Copper
Material Type - Screw	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
UPC	781810355763
UPC 12 Digit	7818103557633

Dimensions

Dimension - B Length inch	4.06 in
Dimension - D inch	3.69 in
Dimension - F Width Center to Center inch	1.56 in
Dimension - Height inch	3.69 in
Dimension - L Length Overall mm	64 mm
Dimension - Length Overall inch	2.50 in
Dimension - Length Side A inch	2.50 in
Dimension - Length Side B inch	3.06 in
Dimension - Pad Width inch	1.94 in
Height	3.69 in
Length	2.50 in
Width	4.06 in

Conductor Related

Conductor - Copper Solid Size Range	800 KCMIL - 1000 KCMIL
Conductor - Copper Str Size	800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Size Range	800 kcmil-1000 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)