



GD1529

by Burndy
Catalog ID: GD1529

Prop 65 Notice

Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 2/0 AWG (Sol.) - 200 kcmil, 1-1/8" to 1-1/4" Rod, 1" Pipe, DURIUM #6 (U-Bolt), Hex Nuts & SPLW

Product Details

General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy, Cast
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
U Bolt Type	244
UPC	781810260265
UPC 12 Digit	7818102602655

Dimensions

Dimension - B Length inch	1.13 in
Dimension - Height fraction	3-3/8 in
Dimension - Height inch	3.38 in
Dimension - Width fraction	2-5/8 in
Dimension - Width inch	2.63 in
Dimension - Width mm	67 mm

Conductor Related

Conductor - Copper Solid Size	2/0;3/0;4/0
Conductor - Copper Solid Size Range	2/0-4/0
Conductor - Copper Str Size	2/0;3/0;4/0;250
Conductor - Copper Str Size B Range	1
Conductor - Copper Str Size Range	2/0-250
Conductor - Copper Tube Std Size	1-1/8;1-1/4
Conductor - Copper Tube Std Size Range	1-1/8-1-1/4
Conductor - Rod Size	1 1/4 in
Conductor - Rod Size Range	1 1/4 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	4
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)