



GD1829W

by Burndy
Catalog ID: GD1829W

Prop 65 Notice

ACCOM: A - 2 IPS 2" O.D. TUBE B - 250 kcmil (.575 DIA) TO 2/0 SOL (.360 DIA) CU

Product Details

General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	Y
Plating Type	Tin - Hot Dipped
U Bolt Type	257
UPC	781810099926
UPC 12 Digit	7818100999266

Dimensions

Dimension - B Length inch	1.31 in
Dimension - Width fraction	3-2/3 in
Dimension - Width inch	3.69 in
Dimension - Width mm	94 mm

Conductor Related

Conductor - Copper Solid Size	2/0;3/0;4/0
Conductor - Copper Solid Size Range	2/0-4/0
Conductor - Copper Str Size	2/0;3/0;4/0;250
Conductor - Copper Str Size B Range	2
Conductor - Copper Str Size Range	2/0-250
Conductor - Copper Tube Std Size	2
Conductor - Copper Tube Std Size Range	2

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467

Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)