



GD2126

by Burndy
Catalog ID: GD2126

Prop 65 Notice

Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 4 AWG (Sol.) - 2/0 AWG (Str.), 3-1/2" to 4" Rod, 3-1/2" Pipe.

Features: High Copper Alloy Ground Connector For Joining A Range Of Two Parallel Cables To Rod Or Pipe, Especially Good For Grounding Fence Posts, High Copper Alloy Cast Body With DURIMUM U-Bolts, Nuts, And Lockwashers Make The GD Suitable For Burial In Ground Or Concrete, One-Wrench Installation, UL467 Listed, Acceptable For Direct Burial In Earth Or Concrete, Raised Floor: No, Ground Rod Size: 3-1/2 - 4 IN, Tube (ips) Size: 3-1/2 IN, Height: 6-1/4 IN, Installation Torque: 240 IN-LB, Width: 5-3/8 IN

Product Details

General

Application	For Joining A Range Of Two Parallel Copper Cables To Rod Or Pipe And Burial In Ground Or Concrete
Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy, Cast
Material Type - Screw	DURIMUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GD
U Bolt Type	264
UPC	781810260425
UPC 12 Digit	7818102604255

Dimensions

Dimension - B Length inch	1.50 in
Dimension - Height fraction	6-1/4 in
Dimension - Height inch	6.25 in
Dimension - Width fraction	5-3/8 in
Dimension - Width inch	5.31 in
Dimension - Width mm	135 mm

Conductor Related

Conductor - Copper Solid Size	4;3;2;1;1/0;2/0
Conductor - Copper Solid Size Range	4-2/0
Conductor - Copper Str Size	4;3;2;1;1/0;2/0
Conductor - Copper Str Size B Range	3.5
Conductor - Copper Str Size Range	4-2/0
Conductor - Copper Tube Std Size	3-1/2
Conductor - Copper Tube Std Size Range	3-1/2

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)