



GD2234

by Burndy
Catalog ID: GD2234

Prop 65 Notice

Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 300 - 500 kcmil, 4" to 4-1/2" Pipe, 4" Rod

Product Details

General

Installation Torque Recommended in-lb	480 LBS/in
Material	Copper Alloy, Cast
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
U Bolt Type	262
UPC	781810260470
UPC 12 Digit	7818102604700

Dimensions

Dimension - B Length inch	1.38 in
Dimension - Height fraction	6-7/8 in
Dimension - Height inch	6.88 in
Dimension - Width fraction	6-1/4 in
Dimension - Width inch	6.19 in
Dimension - Width mm	157 mm

Conductor Related

Conductor - Copper Str Size	300;350;400;450;500
Conductor - Copper Str Size B Range	4
Conductor - Copper Str Size Range	300-500
Conductor - Copper Tube Std Size	4
Conductor - Copper Tube Std Size Range	4
Conductor Size	300 kcmil - 500 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467

Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)