



GG161W

by Burndy
Catalog ID: GG161W

RUN: IPS: 1 1/4" ROD: 1 3/8" - 1 1/2"

Product Details

General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	Y
Plating Type	Tin - Hot Dipped
U Bolt Type	204
UPC 12 Digit	0

Dimensions

Dimension - B Length inch	1.38 in
Dimension - Braid Width Max fraction	1 in
Dimension - Braid Width Max inch	1.00 in
Dimension - Height inch	3.50 in
Dimension - Width fraction	3 in
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

Conductor Related

Conductor - Copper Str Size B Range	1.25
Conductor - Copper Tube Std Size	1-1/2
Conductor - Copper Tube Std Size Range	1-1/2
Conductor Type	<ul style="list-style-type: none"> Rod-Size CU Tube Std-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467

Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)