



GG1815

by Burndy
Catalog ID: GG1815

Prop 65 Notice

Mechanical Grounding Connector, Copper Bar, Strap, Braid or Cable to Rod or Tube, 2" Pipe, 2"-2 3/8" Rod.

Features: High Copper Alloy Ground Connector For Joining Bar, Strap, Braid Or Cable To Rod Or Tube, High Copper Alloy Cast Body, DURIMUM U-Bolts, Nuts And Lockwashers Make The GG Particularly Effective For Use With Braid For Ground Rods, Switch Handles, Fence Posts And Gates, One-Wrench Installation, Dimension A: 1-1/2 IN, Tube (ips) Size: 2 IN, Ground Rod Size: 2 - 2-3/8 IN, Installation Torque: 240 IN-LB, Height: 4-1/4 IN, Width: 3-3/4 IN

Product Details

General

| | |
|---------------------------------------|--|
| Application | For Joining Copper Bar, Strap, Braid Or Cable To Rod Or Tube, Direct Burial Cables |
| Installation Torque Recommended in-lb | 480 LBS/in |
| Material | Copper Alloy, Cast |
| Material Type - Screw | DURIMUM™ Silicon Bronze |
| Plated | N |
| Plating Type | Unplated |
| Sub Brand | MECHANICAL CONNECTOR |
| Type | GG |
| U Bolt Type | 257 |
| UPC | 781810260074 |
| UPC 12 Digit | 7818102600744 |

Dimensions

| | |
|---------------------------|---------|
| Dimension - B Length inch | 1.50 in |
| Dimension - Width inch | 3.69 in |
| Dimension - Width mm | 94 mm |

Conductor Related

| | |
|----------------------------------|---------|
| Conductor - Copper Tube Std Size | 2;2-1/4 |
|----------------------------------|---------|

Certifications and Compliance

| | |
|---|-------|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Listed Direct Burial | Yes |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | EX |

| |
|-----------|
| UL Listed |
|-----------|

| |
|----|
| No |
|----|

Logistics

| |
|-----------------------|
| Minimum Pack Quantity |
|-----------------------|

| |
|---|
| 1 |
|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)