

GG181SE

by Burndy
Catalog ID: GG181SE

Cast Cu Alloy Ground Connector, 2" IPS, 2" - 2-3/8" Rod, 3/8" Bolt



Product Details

General

| | |
|---------------------------------------|------------------------|
| Installation Torque Recommended in-lb | 240 LBS/in |
| Material | Copper Alloy |
| Material Type - Screw | DURIUM™ Silicon Bronze |
| Plated | N |
| Plating Type | Unplated |
| U Bolt Type | 257 |
| UPC | 621945496811 |
| UPC 12 Digit | 0 |

Dimensions

| | |
|--------------------------------------|----------|
| Dimension - B Length inch | 1.38 in |
| Dimension - Braid Width Max fraction | 1 in |
| Dimension - Braid Width Max inch | 1.00 in |
| Dimension - Height inch | 4.25 in |
| Dimension - Width fraction | 3-2/3 in |
| Dimension - Width inch | 3.69 in |
| Dimension - Width mm | 94 mm |

Conductor Related

| | |
|--|--|
| Conductor - Copper Str Size B Range | 2 |
| Conductor - Copper Tube Std Size | 2;2-1/4 |
| Conductor - Copper Tube Std Size Range | 2-2-1/4 |
| Conductor Type | <ul style="list-style-type: none"> Rod-Size CU Tube Std-Size |

Certifications and Compliance

| | |
|---|-----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Listed Direct Burial | Yes |
| Certification - UL Recognized | No |
| Certification - cULus | No |

| | |
|------------------------------------|-------|
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | EX |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)