



GG181

by Burndy
Catalog ID: GG181

Prop 65 Notice

Mechanical Grounding Connector, Copper Bar/Strap/Braid/Cable to Rod/Tube, 2" Pipe, 2"-2-3/8" Rod.

Features: High Copper Alloy Ground Connector For Joining Bar, Strap, Braid Or Cable To Rod Or Tube, High Copper Alloy Cast Body, DURIMUM U-Bolts, Nuts And Lockwashers Make The GG Particularly Effective For Use With Braid For Ground Rods, Switch Handles, Fence Posts And Gates, One-Wrench Installation, Dimension A: 1 IN, Tube (ips) Size: 2 IN, Ground Rod Size: 2 - 2-3/8 IN, Width: 3-3/4 IN, Installation Torque: 240 IN-LB, Height: 4-1/4 IN

Product Details

General

Application	For Joining Copper Bar, Strap, Braid Or Cable To Rod Or Tube, Direct Burial Cables
Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy, Cast
Material Type - Screw	DURIMUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GG
U Bolt Type	257
UPC	781810260067
UPC 12 Digit	7818102600677

Dimensions

Dimension - B Length inch	1.38 in
Dimension - Width inch	3.69 in
Dimension - Width mm	94 mm

Conductor Related

Conductor - Copper Tube Std Size	2;2-1/4
----------------------------------	---------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467

Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)