



GK1434

by Burndy
Catalog ID: GK1434

Prop 65 Notice

Mechanical Grounding Connector, 3 Cables to Rod or Pipe, 300 kcmil - 500 kcmil, 1/2" - 3/4" Pipe, 7/8" - 1" Rod, 1/2" Stud

Product Details

General

Installation Torque Recommended in-lb	480 LBS/in
Material	Copper Alloy, Cast
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Type	Three Cables to Rod or Tube
UPC	781810233696
UPC 12 Digit	7818102336966

Dimensions

Bolt Size	1/2 in
Dimension - B Length inch	1.75 in
Dimension - Height inch	3.69 in
Dimension - Width inch	4.10 in
Dimension - Width mm	104 mm

Conductor Related

Conductor - Rod Size	7/8 in;1 in
Conductor - Rod Size Range	7/8 in-1 in
Conductor Size	300 kcmil - 500 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)