



GK1829

by Burndy
Catalog ID: GK1829

Prop 65 Notice

Mechanical Grounding Connector, 3 Cables to Rod or Pipe, 2/0 AWG (Sol.) - 250kcmil, 2" Pipe, 2" - 2-3/8" Rod, 1/2" Stud.

Features: High Copper Alloy Ground Connector For Joining Three Equal Cables To Rod Or Tube, Cable Grooves Take A Wide Range Of Cable, High Copper Alloy Cast Body And DURIMUM U-Bolts, Nuts, And Lockwashers Make The GK Suitable For Direct Burial In Soil Or Concrete, One-Wrench Installation, UL467 Listed, Acceptable For Direct Burial In Earth Or Concrete, Ground Rod Size: 2 - 2-3/8 IN, Tube (ips) Size: 2 IN, Installation Torque: 480 IN-LB, Width: 5-1/8 IN, Height: 4-3/8 IN

Product Details

General

Application	For Joining Three Equal Copper Cables To Rod Or Tube, Direct Burial In Earth Or Concrete
Installation Torque Recommended in-lb	480 LBS/in
Material	Copper Alloy, Cast
Material Type - Screw	DURIMUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	Three Cables to Rod or Tube
UPC	781810233627
UPC 12 Digit	7818102336277

Dimensions

Bolt Size	1/2 in
Dimension - B Length inch	1.63 in
Dimension - Height inch	4.38 in
Dimension - Width fraction	5-1/8 in
Dimension - Width inch	5.13 in
Dimension - Width mm	130 mm

Conductor Related

Conductor - Rod Size	2 in; 2 7/8 in
Conductor Size	2/0 AWG Sol - 250 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No

Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	4
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)