



GK1926W

by Burndy
Catalog ID: GK1926W

Prop 65 Notice

IPS: 2 - 1/2" ROD: 2 - 1/2, 2 - 7/8" CABLE: 4 SOL. - 2/0 STR.

Product Details

General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	Y
Plating Type	Tin - Hot Dipped
Type	Three Cables to Rod or Tube
U Bolt Type	266
UPC	781810117576
UPC 12 Digit	7818101175766

Dimensions

Dimension - B Length inch	1.50 in
Dimension - Height inch	5.00 in
Dimension - Width fraction	5 in
Dimension - Width inch	5.06 in
Dimension - Width mm	129 mm

Conductor Related

Conductor - Copper Solid Size	4;3;2;1;1/0;2/0;3/0
Conductor - Copper Solid Size Range	4-3/0
Conductor - Copper Str Size	5;4;3;2;1;1/0;2/0
Conductor - Copper Str Size B Range	2.5
Conductor - Copper Str Size Range	5-2/0
Conductor - Copper Tube Std Size	2;2-1/4;2-1/2;2-3/4
Conductor - Copper Tube Std Size Range	2-2-3/4

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No

Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)