



GK1929

by Burndy
Catalog ID: GK1929

Prop 65 Notice

Mechanical Grounding Connector, 3 Cables to Rod or Pipe, 2/0 AWG (Sol.) - 250 kcmil, 2-1/2" Pipe, 2-1/2" - 2-7/8" Rod, 1/2" Stud

Product Details

General

Installation Torque Recommended in-lb	480 LBS/in
Material	Copper Alloy, Cast
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Type	Three Cables to Rod or Tube
UPC	781810233559
UPC 12 Digit	7818102335599

Dimensions

Bolt Size	1/2 in
Dimension - B Length inch	1.63 in
Dimension - Height inch	5.00 in
Dimension - Width fraction	5-5/8 in
Dimension - Width inch	5.63 in
Dimension - Width mm	143 mm

Conductor Related

Conductor - Rod Size	2 1/2 in; 2 7/8 in
Conductor Size	2/0 AWG Sol - 250 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)