



GK2034

by Burndy
Catalog ID: GK2034

Mechanical Grounding Connector, 3 Cables to Pipe or Rod, 300 kcmil - 500 kcmil, 3" Pipe, 3 or 3-1/2" Rod, 1/2" Stud

Product Details

General

Installation Torque Recommended in-lb	480 LBS/in
Material	Copper Alloy, Cast
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Type	Three Cables to Rod or Tube
UPC	621945128842
UPC 12 Digit	6219451288422

Dimensions

Bolt Size	1/2 in
Dimension - B Length inch	1.75 in
Dimension - Height inch	6.31 in
Dimension - Width fraction	6-7/8 in
Dimension - Width inch	6.88 in
Dimension - Width mm	175 mm

Conductor Related

Conductor - Rod Size	3 in ; 3 1/2 in
Conductor Size	300 kcmil - 500 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)